

The Semet's Stretch Comparison Chart

SEMET'S STRETCH 101

All you need to know about **Semet** products.



Semet Hand Stretch Comparison Chart

	Thickness Intervals (µm)	Elongation	Width	Lenght	Re-cycle	Puncture Resistance	Holding Power
Standard	15µ - 35µ	125%	40-45-50 CM	100-500 M		●●●●○	●●●●●
Premium Grade	10µ - 12µ - 14µ	175%	40-45-50 CM	300-600 M		●●●●○	●●●●●
Premium Plus	8µ - 10µ - 12µ	60%	40-45-50 CM	300-600 M		●●●●●	●●●●●
S+S+S	10µ - 12µ - 14µ - 16µ	100%	40-45-50 CM	300-600 M		●●●●●	●●●●○
%51	8µ - 10µ - 12µ 14µ - 16µ	250%	40-45-50 CM	300-600 M		●●●●○	●●●●●
S+S	10µ - 16µ	150%	40-45-50 CM	300-600 M		●●●●●	●●●●●
Pre Stretch	4µ to 12µ	20%	38CM to 43CM	300-600 M		●●●○	●●●○
V.T.S.S.	10µ - 12µ - 14µ - 16µ	150%	40-45-50 CM	300-600 M		●●●●●	●●●●●



Semet Machine Stretch Comparison Chart

	Thickness Intervals (µm)	Elongation	Width	Lenght	Re-cycle	Puncture Resistance	Holding Power
%150 Power	15µ - 35µ	150%	25 - 50 CM	1000-1500 M		●●●○●	●●●●●
%200	15µ - 35µ	200%	25 - 50 CM	1000-1500 M		●●●●○	●●●●●
%250 Super Power	15µ - 35µ	250%	25 - 50 CM	1000-1500 M		●●●●○	●●●●●
%300	15µ - 35µ	300%	25 - 50 CM	1000-1500 M		●●●●●	●●●●○
%350 Max Power	15µ - 35µ	350%	25 - 50 CM	1000-1500 M		●●●●●	●●●●●
Premium Plus	10µ - 12µ - 15µ	10µ : 250% 12µ&15µ : 350%+	25 - 50 CM	1000-3000 M		●●●●●	●●●●●
S+S+S	10µ - 12µ - 14µ - 16µ	10µ&12µ : 200%+ 14µ&16µ : 250%+	25 - 50 CM	1000-3000 M		●●●●○	●●●○●
Pre Stretch	4µ to 12µ	20%	38 - 50 CM	1000-3000 M		●●●●○	●●●●○
Slippery Premium Plus	10µ - 12µ - 15µ	10µ : 250% 12µ&15µ : 350%+	25 - 50 CM	1000-3000 M		●●●●●	●●●○●